

Automatic metal-edge filter AF 71 H

with radial scraper cleaning High-pressure design up to 400 bar

1. Features

MAHLE automatic metal-edge filters are suitable for all applications where low or high-viscosity liquids or pastes have to be filtered and homogenised.

These compact, inline filter systems are designed for automatic cleaning. The system is cleaned by rotating the filter cartridge against a spring actuated scraper.

Advantages:

- Extended filter service life due to the use of a cleanable element
- Cleaning is possible without interrupting filtration
- Precise separation quality in accordance with the metal-edge principle
- Sturdy filter cartridge made of triangular stainless steel wire on a rugged core element
- Efficient filter cleaning assures maximum process stability
- Solid construction and high-quality materials for a long service life
- Optimal filter selection
- Material variants open up a wide range of applications
- Easy maintenance
- Worldwide distribution



2. Operating principle

The MAHLE AF 71 H is a special type of metal-edge filter. The MAHLE metal-edge filter system with an operating pressure up to 400 bar is used to filter and homogenise a wide range of liquids and pastes.


This compact, inline filter system consumes no filter material, which means there is also no need for subsequent disposal. The filter is cleaned automatically, semi-automatically or manually without interrupting operation. The concentrated solids are drained off simply by opening the system for a short time.

The medium to be cleaned is guided into the filter housing under pressure or in suction mode. It flows inward through the MAHLE filter cartridge. The solids are separated on the surface of the triangular filter cartridge wires. The filtered fluid exits the filter housing at the top opposite the inlet connection.

The filter is cleaned either when a preset differential pressure limit is reached or after a specified cycle time elapses. The MAHLE filter cartridge is rotated against a spring actuated scraper for this purpose. The special gap geometry of the filter cartridge guarantees efficient cleaning.

The particles or agglomerates are skimmed from the surface and settle in the collection cone. The patented filter cartridge bearing (AKF system) prevents high axial forces and facilitates the cleaning process.

The residue that has settled in the collection plenum can be emptied via the drain valve either when the machine is at a standstill or during filtration if there are moderate pessure conditions.



Used MAHLE filter cartridges in the AF 71 H metal-edge filter:

MAHLE coiled cartridge (standard):


- Optimum cleaning by means of sharp-edged triangular wire
- Large effective filter surface
- Small, precise gap widths
- High differential pressure stability and torsional strength
- Several material combinations possible

MAHLE welded cartridge:

- High wear resistance to abrasive media
- Sturdy trapezoidal wire for high-viscosity media
- Welded design
- Manufactured in stainless steel



- 1 Inlet connection
- 2 Inlet plenum
- 3 MAHLE filter cartridge
- 4 Triangular wire winding
- 5 Plenum for filtered fluid
- 6 Outlet connection
- 7 Particle collection plenum
- 8 Scraper
- 9 Cleaning drive with gear motor or hand ratchet
- 10 Drain valve manual



- Cleaning drive, worm gear motor can be mounted at each 90° position
- 2 Ratchet optional
- 3 Name-plate
- 4 Mounting holes Ø13
- 5 Drain valve manual, automatic mode optional
- 6 Clearance required = 260 mm

Optional: differential pressure switch

Filter data

Max. operating pressure:

Max. operating

400 bar

temperature: 100 °C

Materials: - Filter head: Nodular cast iron 40

Filter bowl: Ck 15Internals: St. 1.4301, nodular cast iron

- Bearing bushes: PTFE based

- Seals: FPM (Viton)

 Coiled cartridge: 1.4571 or 1.4571/Al (∆p max. 40 bar)
Welded cartridge: 1.4571

(∆p max. 10 bar)

Connections and nominal

diameters:

- A-inlet, B-outlet: G11/4

C-drain: G1/2

- All threaded holes acc. to

DIN 3852 form X

Drive shaft seal: Cup seal packing

and O-ring

Outside coating: Synthetic resin primer, blue

acc. to RAL 5007

Motor data

Worm gear motor Multi-range winding

V	Hz	kW	rpm	Α
Δ 230 ± 10%	50	0.18	17	1.2
人 400 ± 10%	50	0.18	17	0.7
△ 266 ± 10%	60	0.22	21	1.2
人 460 ± 10%	60	0.22	21	0.7

Protection class: IP55, insulation class F; output torque: 52 Nm

Optional: Ex Protection acc. to ATEX 94/9/EC

- Electrical design in Ex II 2G T3
- Mechanical design in Ex II 2G c T3

Weight: 10 kg (with ratchet) or 14 kg (with motor)

Volume: 2.5 I

Other types available on request!


Technical data is subject to change without notice!

4. Design and application

Cartridge type (see section 6)	Total surface in cm ²	Gap width in μm/ effective filter surface in cm²														
		30	40	50	60	80	100	130	160	200	250	360	500	1000	1500	2000
AF 7013	230	14	18	22	26	33	40	50	59	69	81	102	121	162	182	194
AF 7033	230	14	18	22	26	33	40	50	59							
AF 7073	230						22	28	33	40	49	64	81	121	146	162
AF 7083	230			15	18	23	29	36	43	51	61	79	97	139	162	177

Recommended design

Cleaning and emptying



Operation mode:

Filtration usually takes place under pressure. The filter is cleaned after a programmed time or a preset number of cycles or according to the differential pressure. We recommend cleaning the system at approximately 4 times the initial differential pressure. The cleaning motor is operated for around 10 seconds (about three turns of the filter cartridge). This is sufficient to clean the filter thoroughly. The motor may need to run continuously in exceptional cases. The drive shaft is always turned clockwise.


The drain valve is opened in order to empty the filter. Depending on the residue concentration, this can either take place synchronously with cleaning or be time or cycle controlled.

The opening time of the drain valve can be between 2 and 6 seconds. The filter can be emptied in suction mode using a buffer or by interrupting the filtration process.

Semi-automatic and manual operation are also possible.

Refer to the Instruction Manual for further information.

5. Efficiency curves



6. Type number key

Type number key with selection example for AF 7132-1691-60101/H1 Size **AF 713** 1 x 42x190 No. of steps x diameter x length [mm] Cleaning drive Ratchet Gear motor 230/400 V, 50 Hz or 266/460 V, 60 Hz Gear motor 230/400 V, 50 Hz Ex II 2G T3 Inlet and outlet connections G11/4 Permissible operating pressure in bar (housing/cover) PN 400 Material Seal FPM, bearing PTFE Housing and cover nodular cast iron, steel, aluminium Housing and cover steel, grey cast iron or nodular cast iron, internals stainless steel 1.4301/1.4571 Differential pressure indicator PiS 3192, switching level at 2.2 bar, static 450 bar PiS 3192, switching level at 5 bar, static 450 bar Valves and control throttles for AF 11, 13, 15, 17 Without/special version Drain valve Ball valve, manual 1 2 Ball valve, electropneumatic 24 V 3 Ball valve, electropneumatic 230 V 4 Ball valve, electric 24 V Ball valve, electric 230 V Cleaning valve Without/special version **Optional features** Without/special version Bypass valve 20 bar **AF 713** 2 - 16 9 -6 0 1 0 -XXXX (end number for special version)/H1

End number	Special version
3700	PTFE seals
Other numbers	On request

es								/E1				
AF 70	Coiled or welded cartridge with triangular wire winding											
	Material	Core e	lement	Filter medium	Clamp rings	Wire width in mm						
	Coiled car	tridge										
1			Al	1.4571	1.4571							
	3		1.4581	1.4571	-	0.5						
	Welded cartridge											
	7		-	1.4571	1.4571							
	8		-	1.4571	1.4571	0.75						
		Overall length Diameter x length in mm										
		3 42x190										
		Gap wid	th/rating in µm ((see 4. Design and app	lication)							
		003	30 µm	010	100 μm	036	360 µm					
		004	40 µm	013	130 µm	050	500 µm					
		005	50 µm	016	160 µm	100	1000 µm					
	006		60 µm	020	200 μm	150	1500 µm					
		800	80 µm	025	250 μm	200	2000 µm					
			Other filter rati	ngs on request								
AF 70	1	3 -010						/E				

7. Spare parts

No.	Designation	Material no.			
		FPM/C steel	PTFE/VA		
1	Bush kit		79797184		
2	Seal kit (complete)	79797176			
3	Scraper		78389447		
4	Filter cartridge	See name-	plate		

Please contact us for detailed technical information, any open questions about options, accessories and for general expert advice. Completion of the relevant questionnaire would facilitate in the coordination of all important parameters.

Comprehensive documentation on our filter range, filter elements and accessories can be provided. About installation and operation, please refer to the Instruction Manual

MAHLE Filtersysteme GmbH Industriefiltration Schleifbachweg 45 D-74613 Öhringen Phone +49 (0) 7941/67-0 Fax +49 (0) 7941/67-23429 industriefiltration@mahle.com www.mahle-industrialfiltration.com 76122550.03/2010